


# AseptoPowder



Powerful alkaline, chlorine-free cleaner for milking equipment and milk tanks.

- ▲ Chlorine free
- ▲ Readily soluble powder

## APPLICATION

Pre-clean with water. Clean with **AseptoPowder** at 0.5% (minimum 10 min. at 40°C - 50°C). Rinse with water of drinking quality. To be used in rotation with **HorolithPowder**.



## FEATURES AND BENEFITS

**AseptoPowder** is an alkaline cleaner for use in all kinds of milking equipment, including cooling tanks. It has very good cleaning properties and is free of chlorine. **AseptoPowder** is readily soluble.

The **Powder** products are suitable for use with all water hardnesses.

## SPECIFICATIONS

AseptoPowder	
Physical Form	Light yellow powder
Active Substance	Sodium hydroxide, complexing agents
pH at 20°C:	11.5 - 12.5
Density at 20°C (g/cm <sup>3</sup> ):	1.6 - 1.7
Storage temperature:	-10°C to +40°C

## LOGISTICS

Packaging	11 kg	20 kg
Product code	2331620	2331630
EAN code	4028162331622	4028162331639

A Material Safety Data Sheet is available on request for professional users.  
A Product Data Sheet is available on request.