



3 way valve for calibration



Elados diaphragm pumps with overpressure safety valves and/or snubbers against pressure shocks



Dedicated flowmeter or rotameter for each product line



Distribution valve block

ELADOS Compact

New Generation of Dispensing Solution for Tunnel Washers

MAIN FEATURES

- ◆ Supply of 5 dosing points per tunnel washing machine with 2 to 4 products
- ◆ Flowmeter (OGM+)
- ◆ Leak detection
- ◆ Integrated splash protection
- ◆ Flush for each line to the DP's
- ◆ Pumps related to compartments
- ◆ Max. 5 OGM+ / Rotameter optional
- ◆ ULTRAX Compact valve block

BENEFITS

- ◆ Quick installation
- ◆ Space saving by compact design
- ◆ Electric devices have no contact to chemicals
- ◆ Modular design, configuration can be customised